



VF318PZF

Small distributor,golf,flush,MM,54M,3row,white door,slotted

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	54
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	543 mm
Width	460 mm
Depth	97.50 mm
Built-in width	426 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	72 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	Yes

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability	
RoHS conform	Yes