



GD104T

Mini-enclosure, GD, 6 module wide, protect. class IP30, without door

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	50 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	6
-------------------	---

Dimensions

Height	180 mm
Width	146 mm
Depth	82 mm
Number of width units	6

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes