



GD106N

Mini-enclosure, gamma, 6 module, protect. class IP30, 1xPE, 1xN

### Technical Features

#### Voltage

Nominal voltage 230 - 230 V

#### Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

#### Electric current

Rated current 50 A

#### Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

#### Capacity

Number of modules 6

#### Functions

Has protection main switch No

With conduit inlets Yes

#### Dimensions

Height 180 mm

Width 146 mm

Depth 82 mm

#### Cover, door

Number of locks 0

#### Dimensions

Number of width units 6

#### Cover, door

Door/cover is transparent No

#### Connectivity

Mounting type Screw mounting

#### Materials

Material Plastic

RAL code 9010

Colour Pure white

#### Equipment

Has earthing terminal block Yes

Has mounting plate No

#### Safety

Protection class Isolation class II

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Locking type Without lock

Glow wire test 750 °C

#### Sustainability

RECh-SVHC free Yes