



GD106E

Mini-enclosure, gamma, 6 module, protect. class IP30, 1xPE

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	50 A
---------------	------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Capacity

Number of modules	6
-------------------	---

Functions

Has protection main switch	No
----------------------------	----

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	180 mm
--------	--------

Width	146 mm
-------	--------

Depth	82 mm
-------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	6
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class II
------------------	--------------------

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP30
-------------------------------	------

Locking type	Without lock
--------------	--------------

Glow wire test	750 °C
----------------	--------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----