



GD104N

Mini-enclosure, gamma, 4 module, protect. class IP30, 1xPE, 1xN

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	40 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	4
-------------------	---

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	180 mm
Width	110 mm
Depth	82 mm

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	4
-----------------------	---

Cover, door

Door/cover is transparent	No
---------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes