



GD102B

**Mini-enclosure, gamma, 2 module, protect. class IP30**

**Technical Features**

**Voltage**

Nominal voltage	230 - 230 V
-----------------	-------------

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Electric current**

Rated current	32 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	2
-------------------	---

**Dimensions**

Height	160 mm
Width	55 mm
Depth	82 mm
Number of width units	2

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes