



GD102E

### Mini-enclosure, gamma, 2 module, protect. class IP30

#### Technical Features

##### Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	32 A
---------------	------

##### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

##### Capacity

Number of modules	2
-------------------	---

##### Functions

Has protection main switch	No
With conduit inlets	Yes

##### Dimensions

Height	160 mm
Width	55 mm
Depth	82 mm

##### Cover, door

Number of locks	0
-----------------	---

##### Dimensions

Number of width units	2
-----------------------	---

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

##### Equipment

Has earthing terminal block	No
Has mounting plate	No

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes