



FL154A

**Steel enclosure, Orion.Plus, glazed door 350x300x160 mm**

**Technical Features**

**Dimensions**

Height	350 mm
Width	300 mm
Depth	160 mm
Thickness of sidewall	1.20 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

**Equipment**

Number of section in width	0
Number of flange plate openings	2

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	No

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

**Equipment**

Number of rows	2
----------------	---

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	Yes

**Electric current**

Rated current	250 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----