



EV106



**Remote control dimmer 1-10V**

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Connectivity**

Dimming DALI	No
--------------	----

**Power**

Power consumption during operation	3 VA
------------------------------------	------

Power consumption standby	1 W
---------------------------	-----

**Use conditions**

Operating temperature	-10 - 45 °C
-----------------------	-------------

**Dimensions**

Height	85 mm
--------	-------

Width	71 mm
-------	-------

Depth	65 mm
-------	-------

**Connection**

Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
-------------------------------	--------------------------

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
----------------------------------	-----------------------

**Capacity**

Number of modules	4
-------------------	---

**Electric current**

Control current 1-10 V slave	50 mA
------------------------------	-------

**Materials**

Colour	Grey
--------	------

**Texts**

Type of connection	With screw terminals
--------------------	----------------------

Installation mode	For mounting on DIN rail
-------------------	--------------------------

Junction	Connection for illuminated (max. 5 mA) or standard push-buttons
----------	---