



**16AX DND&MUR SWITCH W/ LED (INDOOR)**

**Technical Features**

**Electric current**

Switching current	16 A
-------------------	------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	White
--------	-------

Surface finish	Glossy
----------------	--------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Untreated
-----------	-----------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	2
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
------------	------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Double push button
---------------------------	--------------------

**Electric current**

Rated current	16 A
---------------	------

**Texts**

Switch mode	1x change-over contact and 1NO contact
-------------	--

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----