



WGCHDC

16AX DND&MUR SWITCH W/ LED (INDOOR)

Technical Features

Electric current

Switching current 16 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 86 x 86 mm

Electric current

Rated current 16 A

Sustainability

REACH-SVHC free Yes

RoHS conform Yes