



WGCXL12NB

16AX 1G 2W switch;nb

Technical Features

Electric current

Switching current 16 A

Voltage

Rated voltage 250 V

Materials

Colour Bronze

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 16 A

Texts

Switch mode 2-way

Sustainability

RoHS conform Yes