



FL162A

**Steel enclosure, Orion.Plus, glazed door 500x400x100 mm**

**Technical Features**

**Dimensions**

Height	500 mm
Width	400 mm
Depth	200 mm
Thickness of sidewall	1.20 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

**Equipment**

Number of flange plate openings	2
---------------------------------	---

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	No

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

**Equipment**

Number of rows	3
----------------	---

**Cover, door**

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	Yes
Cabinet door type	Single door

**Electric current**

Rated current	250 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----