



WRSSU83FOBSW

**13A FCU Switched with Flex Outlet Brushed Steel White Insert**

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Stainless steel

Surface finish Matt

Material Stainless steel

Treatment Brushed

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 17.50 mm

**Safety**

Ingress Protection (IP) class IP20

**Electric current**

Rated current 13 A

**Texts**

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-pole

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes