



FWB63N3

FWB encl.,univers,IP44,classII,144mod,interaxis 150mm,950x800x161mm

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	14
Number of rows	14
Number of section in width	3
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	144
-------------------	-----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	950 mm
Width	800 mm
Depth	165 mm

Cover, door

Number of cabinet doors	2
Number of locks	1

Dimensions

Number of width units	36
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	No
Has mounting plate	No

Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP44
Locking type	Bar lock

Sustainability

RoHS conform	Yes
--------------	-----