



85656183



KNX radio wall-transmitter 2gang flat solar quicklink, S.1/B.7, al., matt, lacq.

Technical Features

Settings

Supported configuration mode quicklink

Voltage

Operating voltage 3 - 3 V

Equipment

Number of channels 4

Transmitter duty cycle 1 %

Connectivity

Radio protocol KNX Radio

Receiver category 2

Use conditions

Operating temperature -5 - 45 °C

Dimensions

Assembling height 14 mm

Materials

Colour Aluminium

Material Thermoplastic

Safety

Ingress Protection (IP) class IP20

Texts

Function Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Reset function (to factory setting)

Protection With dismantling protection

Voltage Power supply via solar cells

Installation mode For flat surface mounting and extension of combinations

Sustainability

RoHS conform Yes