



FWB63GS

FWB encl. univers,surface mount. IP44,classII,w. transp.door,950x800x161mm,QC

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	18
Number of rows	18
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	216
-------------------	-----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	950 mm
Width	800 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	2
Number of locks	1

#### Dimensions

Number of width units	36
-----------------------	----

#### Cover, door

Type of handle	Latch
Door/cover is transparent	Yes

#### Connection

Number of conduit inlets	12
--------------------------	----

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP44

#### Sustainability

RoHS conform	Yes
--------------	-----