



20266084

Thermostat w. change-over contact and centre plate, Q.x, alu velvety, lacq.

#### Technical Features

##### Electric current

Rated current	5 A
---------------	-----

##### Voltage

Nominal voltage	250 - 250 V
Rated voltage	250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

##### Materials

Colour	Aluminium
RAL code	9006
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished

##### Dimensions

Height	71 mm
Width	71 mm
Depth	47.50 mm

##### Screen

With display	No
--------------	----

##### Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Connection

Type of contacts	1x changeover
------------------	---------------

##### Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

##### Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes