



20266086

Thermostat, change-over contact, centre plate, Q.x, ant. velvety, lacq.

Technical Features

Architecture

Control/operation element Rotative

Electric current

Rated current 5 A

Max. switching current 10 A

Voltage

Nominal voltage 230-230 V

Power supply

Supply voltage 230 V AC

Frequency

Frequency 50 - 60 Hz

Settings

Comfort temperature setpoint 5 - 30 °C

Materials

Colour Anthracite

RAL code 7016

Surface finish Velvety

Material Metal
Plastic

Dimensions

Height 71 mm

Width 71 mm

Depth 47.50 mm

Screen

With display No

Equipment

Switching temperature difference 0.50 K

Type of thermostat Room thermostat

Type of probe Bimetal

With heater Yes

Safety

Ingress Protection (IP) class IP20

Connection

Type of contacts 1x changeover

Compatibility

Type of HVAC control Heating
Cooling

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Without spreader claws

Type of connection With plug-in terminals

Thermal re-circulation With thermal return

Imprint With imprint

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes