



41666084

sock. outl. w. earthing cont. USA/CANADA NEMA 5-15 R, Q.x alu velvety, lacq.

Technical Features

Voltage

Rated voltage 125 V

Electric current

Rated current 15 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium

RAL code 9006

Surface finish Velvety

Material Thermoplastic

Treatment Varnished

Dimensions

Height 71 mm

Width 71 mm

Built-in depth 19 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet NEMA

Rotated central insert No

With hinged lid No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Protection Without enhanced contact protection

Type of connection With screw terminals

Suitable for

Q.x

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes
