



FL112A

### Steel enclosure, Orion.Plus, plain door 500x400x200 mm

#### Technical Features

##### Dimensions

Height	500 mm
Width	400 mm
Depth	200 mm
Thickness of sidewall	1.2 mm

##### Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

##### Equipment

Number of flange plate openings	2
---------------------------------	---

##### Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

##### Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

##### Equipment

Number of rows	3
----------------	---

##### Cover, door

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

##### Electric current

Rated current	250 A
---------------	-------

##### Sustainability

Halogen free	Yes
RoHS conform	Yes