



FL111A

Steel enclosure, Orion.Plus, plain door 500x400x160 mm

Technical Features

Dimensions

Height	500 mm
Width	400 mm
Depth	160 mm
Thickness of sidewall	1.20 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	3
----------------	---

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Electric current

Rated current	250 A
---------------	-------

Sustainability

Halogen free	Yes
RoHS conform	Yes