



FL124A

Steel enclosure, Orion.Plus, plain door 800x600x300 mm

Technical Features

Dimensions

Height	800 mm
Width	600 mm
Depth	300 mm
Thickness of sidewall	1.2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	5
----------------	---

Cover, door

Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	No
Cabinet door type	Single door

Electric current

Rated current	250 A
---------------	-------

Sustainability

Halogen free	Yes
RoHS conform	Yes