



ST301

**Bell transformer 4VA 230/8-12V**

**Technical Features**

**Voltage**

Output voltage	8 - 12 V
Rated operational voltage Ue	230 - 230 V
Output voltage 2	12 V

**Capacity**

Number of modules	2
-------------------	---

**Power**

Power consumption VA	4 VA
Power	4 VA
Power absorbed	4 W

**Dimensions**

Height	111 mm
Width	35 mm
Depth	65 mm
Dimensions	111 x 35 mm

**Safety**

Ingress Protection (IP) class	IP20
Temperature protection	Yes

**Equipment**

Is short-circuit protected	Yes
On/off switch	No

**Voltage**

Rated insulation voltage Ui	4000 V
-----------------------------	--------

**Use conditions**

Operating temperature	-20 - 35 °C
-----------------------	-------------

**Connection**

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Electric current**

Intensity output 1	0.50 A
Intensity output 2	0.33 A
Max. intensity of secondary	0.5 A

**Installation, mounting**

Mounting on	DIN rail
Nominal tightening torque	1.20 - 1.20 Nm

**Compatibility**

Suitable for DIN Rail	Yes
-----------------------	-----

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

