



ST301

Bell transformer 4VA 230/8-12V

Technical Features

Voltage

Output voltage	8 - 12 V
Rated operational voltage Ue	230 - 230 V
Output voltage 2	12 V

Capacity

Number of modules	2
-------------------	---

Power

Power consumption VA	4 VA
Power	4 VA
Power absorbed	4 W

Dimensions

Height	111 mm
Width	35 mm
Depth	65 mm
Dimensions	111 x 35 mm

Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

Equipment

Is short-circuit protected	Yes
On/off switch	No

Voltage

Rated insulation voltage Ui	4000 V
-----------------------------	--------

Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Intensity output 1	0.50 A
Intensity output 2	0.33 A
Rated secondary current (I _{sr})	0.5 A

Installation, mounting

Mounting on	DIN rail
Nominal tightening torque	1.20 - 1.20 Nm

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

