



11357004

Centre plate f.rot. dimmer/potentiometer, setting knob,K.5,steel matt finish

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Metal Stainless steel
Treatment	Untreated

Dimensions

Height	55 mm
Width	71 mm
Depth	20 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP44 in combination with sealing set

Texts

Imprint	Centre plate without imprint
Installation mode	For screw fastening

Suitable for

K.x	
-----	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes