



VU36NE

Encl., Volta, flush, 3x12MOD, IP30, Version NCEE

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

#### Electric current

Rated current	63 A
---------------	------

#### Power

Maximum power loss per cabinet at $\Delta T=20K$	22.50 W
--	---------

#### Equipment

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	36
Number of half modules terminals per rail	72

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	630.50 mm
Width	348 mm
Depth	98 mm
Built-in height	615 mm
Built-in width	314.50 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	89 mm
----------------	-------

#### Cover, door

Number of locks	0
-----------------	---

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

<b>Materials</b>	
Ultraviolet-resistant	Yes
<b>Safety</b>	
Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Snap on lock Without lock
Glow wire test	650 °C
<b>Sustainability</b>	
RoHS conform	Yes