



VU36NR

Encl., Volta, flush, 3x12MOD, IP30, Version Africa

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Suitable for outdoor usage | No             |
| Mounting on                | Flush mounting |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Power

|                                                  |         |
|--------------------------------------------------|---------|
| Maximum power loss per cabinet at $\Delta T=20K$ | 22.50 W |
|--------------------------------------------------|---------|

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rails            | 3  |
| Number of rows             | 3  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

#### Capacity

|                                           |    |
|-------------------------------------------|----|
| Number of modules                         | 36 |
| Number of half modules terminals per rail | 72 |

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|                 |           |
|-----------------|-----------|
| Height          | 630.50 mm |
| Width           | 348 mm    |
| Depth           | 94.50 mm  |
| Built-in height | 615 mm    |
| Built-in width  | 335 mm    |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 90 mm |
|----------------|-------|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

|                               |                              |
|-------------------------------|------------------------------|
| <b>Materials</b>              |                              |
| Ultraviolet-resistant         | Yes                          |
| <b>Safety</b>                 |                              |
| Protection class              | Isolation class II           |
| Ingress Protection (IP) class | IP30                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |
| <b>Sustainability</b>         |                              |
| RoHS conform                  | Yes                          |