



VU36ET

Encl.,Volta,flush,3x12MOD,IP30,Version Spain,transparent door

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Electric current**

Rated current 63 A

**Power**

Maximum power loss per cabinet at  $\Delta T=20K$  22.50 W

**Equipment**

Number of rails 3

Number of rows 3

Number of section in width 1

With lock No

Has neutral terminal block No

**Capacity**

Number of modules 36

Number of half modules terminals per rail 72

**Functions**

With conduit inlets Yes

**Dimensions**

Height 630.50 mm

Width 348 mm

Depth 94.50 mm

Built-in height 615 mm

Built-in width 335 mm

**Cover, door**

Number of cabinet doors 1

**Dimensions**

Built-in depth 90 mm

**Cover, door**

Number of locks 0

**Dimensions**

Number of width units 12

**Cover, door**

Door/cover is transparent Yes

**Connectivity**

Mounting type Screw mounting

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

---

**Materials**

---

Ultraviolet-resistant	Yes
-----------------------	-----

---

**Safety**

---

Protection class	Isolation class II
------------------	--------------------

---

Ingress Protection (IP) class	IP30
-------------------------------	------

---

Locking type	Snap on lock Without lock
--------------	------------------------------

---

Glow wire test	650 °C
----------------	--------

---

**Sustainability**

---

RoHS conform	Yes
--------------	-----

---