



WGDL113EG

### 10AX 1G intermediate switch;eg

#### Technical Features

##### Electric current

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Frequency

Frequency	50-60 Hz
-----------	----------

##### Materials

Colour	Gold
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

##### Identification

Assembly arrangement	Surface-mounted frame
----------------------	-----------------------

##### Connectivity

Mounting type	Screw mounting
With claw mounting	No

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth	25 mm
Built-in depth flush-mounted boxes	35 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	10 A
---------------	------

##### Connection

Type of contacts	1 W + neutral
Connector/plug type	Screw terminal

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	Intermediate

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes