



WGDL113EG

**10AX 1G intermediate switch;eg**

**Technical Features**

**Electric current**

Switching current 10 AX (100W LED (SBL))

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Gold

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

**Identification**

Assembly arrangement Surface-mounted frame

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 25 mm

Built-in depth flush-mounted boxes 35 mm

**Electric current**

Rated current 10 A

**Connection**

Type of contacts 1 W + neutral

Connector/plug type Screw terminal

**Texts**

Lighting Without lighting (cannot be illuminated)

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes