



WGDL113EG

10AX 1G intermediate switch;eg

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Gold

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Identification

Assembly arrangement Surface-mounted frame

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 25 mm

Built-in depth flush-mounted boxes 35 mm

Electric current

Rated current 10 A

Connection

Type of contacts 1 W + neutral

Connector/plug type Screw terminal

Texts

Lighting Without lighting (cannot be illuminated)

Sustainability

REACH-SVHC free Yes

RoHS conform Yes