



WGDL113NB

10AX 1G intermediate switch;nb

Technical Features

Electric current

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Identification

Assembly arrangement	Surface-mounted frame
----------------------	-----------------------

Connectivity

Mounting type	Screw mounting
With claw mounting	No

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	25 mm
Built-in depth flush-mounted boxes	35 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Connection

Type of contacts	1 W + neutral
Connector/plug type	Screw terminal

Texts

Switch mode	Intermediate
-------------	--------------

Sustainability

RoHS conform	Yes
--------------	-----