



47206089

Combination SCHUKO soc. out. 2gang frame, Q.x, p. white velvety

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Velvety

Material Duroplastic

Treatment Untreated

Dimensions

Height 80 mm

Number of units 2

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 2

Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Wiring 2x 1-gang. wired-through

Texts

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

Q.x

Sustainability

Halogen free	Yes
RoHS conform	Yes