



47206086

Combination SCHUKO soc. out. 2gang frame, Q.x, ant. velvety, lacq.

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Anthracite
RAL code	7021
Surface finish	Velvety
Material	Duroplastic
Treatment	Varnished

##### Dimensions

Height	11 mm
Number of units	1
Built-in depth	32 mm

##### Connection

Connector/plug type	Plugable clamp
---------------------	----------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	2
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Central cover plate
Wiring	2x 1-gang. wired-through

<b>Texts</b>	
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

<b>Suitable for</b>	
Q.x	