



41096086



**SCHUKO soc.out. LED orient.,enhncd contact prot.,screw-in lift ,Q.x,ant.velv**

#### Technical Features

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Anthracite    |
| RAL code       | 7021          |
| Surface finish | Velvety       |
| Material       | Thermoplastic |
| Treatment      | Varnished     |

##### Dimensions

|                 |       |
|-----------------|-------|
| Height          | 71 mm |
| Width           | 71 mm |
| Number of units | 1     |
| Built-in depth  | 32 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Connectivity

|                    |                                 |
|--------------------|---------------------------------|
| Type of connection | Screw terminal                  |
| Mounting type      | Screw mounting<br>Claw mounting |

##### Equipment

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert            | No     |
| With hinged lid                   | No     |
| With round protective earth pin   | No     |
| With signal lamp                  | No     |
| With lock                         | No     |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Controls and indicators

|                                               |                              |
|-----------------------------------------------|------------------------------|
| Type of lighting for the installation devices | Integrated orientation light |
|-----------------------------------------------|------------------------------|

##### Safety

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | Yes  |
| Impact resistance IK             | IK05 |
| Ingress Protection (IP) class    | IP20 |

##### Functions

|                           |     |
|---------------------------|-----|
| With orientation lighting | Yes |
| With function lighting    | No  |

##### Identification

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

|                    |                                                                                |
|--------------------|--------------------------------------------------------------------------------|
| <b>Texts</b>       |                                                                                |
| Cover              | Central cover plate                                                            |
| Lighting           | Additional benefit by combination of a socket outlet with an orientation light |
| Wiring             | Through-wiring possible, therefore also ideal for retrofitting                 |
| Protection         | Enhanced contact protection                                                    |
| Type of connection | With screw-in lift terminals                                                   |

|                     |  |
|---------------------|--|
| <b>Suitable for</b> |  |
| Q.x                 |  |

|                       |     |
|-----------------------|-----|
| <b>Sustainability</b> |     |
| Halogen free          | Yes |
| RoHS conform          | Yes |