



WPPS12R



10AX Push Switch

Technical Features

Electric current

| | |
|---------------------------|------|
| Momentary contact current | 10 A |
|---------------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Materials

| | |
|----------------|--------|
| Colour | Grey |
| Surface finish | Glossy |
| Material | Metal |
| Treatment | Epoxy |
| Transparent | No |

Dimensions

| | |
|--------|-------|
| Height | 86 mm |
| Width | 86 mm |
| Depth | 24 mm |

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Controls and indicators

| | |
|------------------------------|--------------------|
| Number of buttons | 1 |
| Type of push button | Single push button |
| With feedback signal contact | No |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|-------------------|-------------------|
| Imprint | Without imprint |
| Installation mode | For wall mounting |
| Switch mode | NO contact |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |