



WPPS12R



10AX Push Switch

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Number of poles 2

Materials

Colour Grey

Surface finish Glossy

Material Metal

Treatment Epoxy

Transparent No

Dimensions

Height 86 mm

Width 86 mm

Depth 24 mm

Installation, mounting

Mounting on Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Texts

Imprint Without imprint

Installation mode For wall mounting

Switch mode NO contact

Sustainability

REACH-SVHC free Yes

RoHS conform Yes