



85341224

IR motion detector comfort 1.1 m, Q.x alu velvety, lacquered

Technical Features

Dimensions

|                     |               |
|---------------------|---------------|
| Installation height | 1.10 - 1.10 m |
| Assembling height   | 34 mm         |

Detection

|                             |                   |
|-----------------------------|-------------------|
| Type of sensor              | Movement detector |
| Detection diameter on floor | 0 - 0 m           |
| Detection angle adjustable  | 45 - 90 °         |

Materials

|                |               |
|----------------|---------------|
| Colour         | Aluminium     |
| Surface finish | Velvety       |
| Treatment      | Varnished     |
| Material       | Thermoplastic |

Reach distance

|                                   |      |
|-----------------------------------|------|
| Max. transmission range frontally | 12 m |
| Max. transmission range sideways  | 8 m  |

Lighting

|                                |             |
|--------------------------------|-------------|
| Response brightness adjustable | 5 - 1000 lx |
|--------------------------------|-------------|

Settings

|                                |     |
|--------------------------------|-----|
| Response brightness adjustable | Yes |
|--------------------------------|-----|

Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

|            |  |
|------------|--|
| Function   | With memory function for presence simulation<br>Teach function for response brightness via button<br>With keylock<br>Party function for switching on for 2 hours |
| Protection | With dismantling protection  |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|