



EG293B



Yearly time switch 2 channels, digital, 4 modules

Technical Features

Voltage

Rated operational voltage U_e 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Power

230 V incandescent and halogen lamp 1500 W

Functions

Power reserve in years 5 y
 With network synchronisation No
 With quartz synchronisation Yes
 Number of function channels 2

Equipment

Accuracy per day 0.20 s
 With impulse programme Yes
 Number of channels 2

Settings

Daily programme No
 Weekly programme No
 Annual programme Yes

Use conditions

Operating temperature -10 - 50 °C

Connection

Cross-section flexible conductor 0.75 - 2.5 mm²
 Cross-section rigid conductor 0.75 - 2.5 mm²

Texts

Type of connection With quickconnect plug-in terminals
 Function With pulse function
 Keylock via PIN
 Presence simulation
 With operating hours meter

Dimensions

Height 90 mm
 Width 70 mm
 Depth 69 mm

Main electrical attributes

Minimum interval between 2 switching times 1 min

Capacity

Number of modules 4

Sustainability

REACH-SVHC free Yes
 RoHS conform Yes