



EG293B



Yearly time switch 2 channels, digital, 4 modules

Technical Features

Voltage

| | |
|--|-------------|
| Rated operational voltage U _e | 230 - 230 V |
|--|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Power

| | |
|-------------------------------------|--------|
| 230 V incandescent and halogen lamp | 1500 W |
|-------------------------------------|--------|

Functions

| | |
|------------------------------|-----|
| Power reserve in years | 5 y |
| With network synchronisation | No |
| With quartz synchronisation | Yes |
| Number of function channels | 2 |

Equipment

| | |
|------------------------|--------|
| Accuracy per day | 0.20 s |
| With impulse programme | Yes |
| Number of channels | 2 |

Settings

| | |
|------------------|-----|
| Daily programme | No |
| Weekly programme | No |
| Annual programme | Yes |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

Connection

| | |
|----------------------------------|----------------------------|
| Cross-section flexible conductor | 0.75 - 2.5 mm ² |
| Cross-section rigid conductor | 0.75 - 2.5 mm ² |

Texts

| | |
|--------------------|---|
| Type of connection | With quickconnect plug-in terminals |
| Function | With pulse function Keylock via PIN Presence simulation With operating hours meter |

Dimensions

| | |
|--------|-------|
| Height | 90 mm |
| Width | 70 mm |
| Depth | 69 mm |

Main electrical attributes

| | |
|--|-------|
| Minimum interval between 2 switching times | 1 min |
|--|-------|

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |