



383620



Change-over switch f. lock cylinders, earth contact, splash-prot. flush-mtd IP44

Technical Features

Electric current

Switching current 16 AX (200W LED (SBL))

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Materials

Material Metal
Plastic
Treatment Untreated

Identification

Assembly arrangement Basic element

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 71 x 71 mm
Built-in depth 31 mm
Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP44

Architecture

Control/operation element Key

Electric current

Rated current 16 A

Texts

Installation mode For screw fastening
Without spreader claws
Type of connection With screw terminals
Switch mode Off/change-over

Sustainability

Halogen free Yes
REACH-SVHC free Yes
RoHS conform Yes