



383620

Change-over switch f. lock cylinders, earth contact, splash-prot. flush-mtd IP44

**Technical Features**

<b>Electric current</b>	
Switching current	16 AX (200W LED (SBL))

<b>Installation, mounting</b>	
Mounting on	Surface mounting

<b>Voltage</b>	
Rated voltage	250 V

<b>Materials</b>	
Material	Metal Plastic
Treatment	Untreated

<b>Identification</b>	
Assembly arrangement	Basic element

<b>Connectivity</b>	
Mounting type	Screw mounting

<b>Controls and indicators</b>	
Number of buttons	1

<b>Dimensions</b>	
Dimensions	71 x 71 mm
Built-in depth	31 mm
Built-in depth flush-mounted boxes	35 mm

<b>Safety</b>	
Ingress Protection (IP) class	IP44

<b>Architecture</b>	
Control/operation element	Key

<b>Electric current</b>	
Rated current	16 A

<b>Texts</b>	
Installation mode	For screw fastening Without spreader claws
Type of connection	With screw terminals
Switch mode	Off/change-over

<b>Sustainability</b>	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes