



BDC840

Earth leakage add-on-block with double output 4P 63A 300mA AC S

Technical Features

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	63 A

Architecture

Number of poles	4
Neutral position	Left

Capacity

Number of modules	3
-------------------	---

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	102 mm
Width	52.50 mm
Depth	70 mm

Illustrations | Drawings

