



TRM694AU



Flush mounted radio output 4A free of potential + 2 inputs mains powered

Technical Features

Connectivity

Radio protocol	KNX Radio
Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

Dimensions

Dimensions	40 x 40 mm
Height	40 mm
Width	40 mm
Depth	20 mm
Built-in depth	40 mm

Electric current

Rated current	4 A
---------------	-----

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

Frequency

Frequency	50 - 50 Hz
Radio reception frequency	433 - 433 MHz

Power

Output power	920 W
230 V incandescent and halogen lamp	600 W

Voltage

Operating voltage	230 - 230 V
Rated operational voltage Ue	230 - 230 V
System supply voltage	230 V AC

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Connection

Cross-section rigid conductor	0.5 - 2.5 mm ²
Cross-section flexible conductor	0.5 - 1.5 mm ²

Texts

Function	Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----