



VM_SIZE_2

2 Way 40A 30mA Type A RCCB Incomer with Knockouts

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Architecture

Number of poles	2
-----------------	---

Capacity

Number of modules	4
-------------------	---

Electric current

Rated current	40 A
---------------	------

Dimensions

Depth	102 mm
Height	240 mm
Width	149 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Equipment

Number of rows	1
----------------	---

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Sustainability

RoHS conform	Yes
--------------	-----