



VM\_SIZE\_2

**2 Way 40A 30mA Type A RCCB Incomer with Knockouts**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Architecture**

Number of poles 2

**Capacity**

Number of modules 4

**Electric current**

Rated current 40 A

**Dimensions**

Depth 102 mm

Height 240 mm

Width 149 mm

**Cover, door**

Interlockable No

Door/cover is transparent No

**Materials**

RAL code 9010

Colour Pure white

Material Steel

**Equipment**

Number of rows 1

**Safety**

Ingress Protection (IP) class IP2XC

**Sustainability**

RoHS conform Yes