



167804

LED lamp E10, light control, blue

Technical Features

Voltage

Nominal voltage 230 - 230 V

Electric current

Rated current 0 A

Dimensions

Height 9.70 mm

Width 9.70 mm

Depth 29 mm

Materials

Colour Blue

Lighting

Type of lamp LED

Use conditions

Operating temperature -40 - 70 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes