



EVN004



## Remote Control Dimmer universal 500W

### Technical Features

#### Voltage

Operating voltage	195.5 - 253 V
Rated operational voltage U <sub>e</sub>	230 - 230 V

#### Connectivity

With bus system KNX radio	No
---------------------------	----

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Grey
RAL code	7035
Material	Plastic

#### Dimensions

Height	85 mm
Width	35 mm
Depth	62 mm

#### Architecture

Control/operation element	Single push button
---------------------------	--------------------

#### Power

Power consumption during operation	4.50 VA
Power consumption standby	0.20 W
230 V incandescent and halogen lamp	500 W
Power incandescent lamp	500 - 500 W

#### Lighting

Dimmable 230 V LED lamp	100 - 100 W
LED lamp power	100 W

#### Use conditions

Operating temperature	-10 - +45 °C
-----------------------	--------------

#### Connection

Cross-section rigid conductor	1.5 - 6 mm <sup>2</sup>
Cross-section flexible conductor	1.5 - 6 mm <sup>2</sup>

#### Capacity

Number of modules	2
-------------------	---

#### Texts

Dimming principle	Automatic load detection
Fuse	With electronic short-circuit and overload protection
Voltage	Others
Installation mode	For mounting on DIN rail
Type of connection	With screw terminals
Junction	Connection for illuminated (max. 5 mA) or standard push-buttons
Operation and control	No Bluetooth interface

#### Equipment

Substation input	No
------------------	----