



JKM02

**Multifunction measurement device DIN rail 2x3-Phase RS485**

**Technical Features**

**Architecture**

Bus system	MODBUS
Type of pole	4P

**Capacity**

Number of modules	4
-------------------	---

**Dimensions**

Height	90 mm
Width	70 mm
Depth	62 mm

**Equipment**

Type of pulse generator	Electrical
-------------------------	------------

**Compatibility**

Suitable for	Purchase
--------------	----------

**Connection**

Connector/plug type	Bus system	Pulse RS485
---------------------	------------	----------------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Measurement**

Measuring system	Measurement transformer
Type of measuring instrument	Electronic
Measurement range voltage Ph-N	60 - 300 V
Measurement range voltage Ph-Ph	104 - 520 V
Frequency measuring range	45 - 65 Hz

**Functions**

Accuracy class	B
Tariff type	One-tariff

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C

**Frequency**

Frequency	45 - 65 Hz
-----------	------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes